

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
60.0	104.13	0.18
61.0	84.41	0.23
62.0	98.95	0.20
63.0	106.85	0.25
64.0	102.13	0.19
65.0	105.51	0.17
66.0	96.65	0.21
67.0	101.77	0.14
68.0	99.97	0.19
69.0	101.33	0.30
70.0	128.15	0.03
71.0	97.99	0.07
71.5	101.81	0.17
72.0	97.51	0.01
72.5	97.95	0.14
73.0	95.41	0.10
73.5	101.57	0.26
74.0	100.23	0.12
74.5	98.00	0.13
75.0	95.28	0.10
75.5	86.50	0.22
76.0	82.50	0.10
76.5	77.68	0.34
77.0	71.28	0.21
77.5	65.17	0.29
78.0	58.19	0.41
78.5	50.22	0.16
79.0	41.78	0.29
79.5	30.82	0.18
80.0	17.39	0.49
80.5	2.12	8.14
81.0	0.72	19.07
81.5	0.58	20.07
82.0	0.15	22.87
82.5	0.48	26.72
83.0	0.52	26.74
83.5	0.35	29.00
84.0	0.47	21.66
84.5	0.47	38.12
85.0	0.44	21.52
85.5	0.59	22.00
86.0	0.44	24.64
86.5	0.59	24.09
87.0	5.80	2.01
87.5	16.62	0.59
88.0	25.78	0.38
88.5	32.78	0.27
89.0	38.89	0.38
89.5	43.77	0.16
90.0	48.31	0.04