

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS Control @ 0V/-5V (dB) IN-OUT , "ON"	ISOLATION Control @ 0V/-5V (dB) IN-OUT , "OFF"	VSWR (:1)		
			IN	OUT , "ON"	OUT , "OFF"
3	0.55	82.53	1.12	1.12	1.02
5	0.55	85.42	1.12	1.12	1.02
10	0.55	84.71	1.13	1.13	1.02
20	0.63	74.57	1.13	1.12	1.02
50	0.62	64.87	1.12	1.12	1.02
100	0.67	58.56	1.12	1.12	1.02
200	0.72	54.29	1.12	1.11	1.02
500	0.80	51.52	1.13	1.12	1.02
912	0.90	48.87	1.16	1.11	1.04
1000	0.90	48.56	1.17	1.10	1.05
1581	1.01	44.26	1.20	1.04	1.11
2107	1.10	39.70	1.30	1.09	1.14
2370	1.15	37.89	1.31	1.11	1.15
2490	1.26	37.25	1.32	1.14	1.17
2753	1.32	35.59	1.41	1.22	1.23
3279	1.26	31.74	1.44	1.35	1.29
3805	1.63	28.75	1.39	1.41	1.38
4331	1.52	25.75	1.49	1.78	1.65
4474	1.47	25.51	1.57	1.94	1.73
4600	1.98	25.42	1.55	1.87	1.67