



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within ± 0.002

| CASE # | A | B | C | D | E | F | G | H | J | K |
|--------|----------------|----------------|----------------|--------|----------------|----------------|----------------|-----------------|----------------|----------------|
| DG1293 | .157 (4.00) | .157 (4.00) | .047 (1.20) | - - | .087 (2.20) | .087 (2.20) | .012 (0.30) | 0.010 (0.25) | .020 (0.50) | .026 (0.65) |

| CASE # | L | M | N | P | Q | R | S | WT. GRAM |
|--------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------|
| DG1293 | .169 (4.30) | .169 (4.30) | .087 (2.20) | .012 (0.30) | .031 (0.80) | .087 (2.20) | .008 (0.20) | .04 |

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

1. Case material: Ceramic.
2. Termination finish: Nickel-Palladium-Gold plating.