



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm.002$

| CASE# | A | B | C | D | E | F | G | H | J | K | L | M | WT. GRAMS |
|-------|---------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|--------------|
| DZ944 | .30 (7.62) | .250 (6.35) | .052 (1.32) | .266 (6.76) | .050 (1.27) | .050 (1.27) | .012 (0.30) | .029 (0.74) | .004 (0.10) | .085 (2.16) | .296 (7.52) | .030 (0.76) | 0.25 |

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3Pl. $\pm .005$

Notes:

- Case material: Ceramic.
- Termination finish:
 - For RoHS Case Styles: Tin plate. All models, (+) suffix.
 - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.