



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	M	N	P
XX112	.180 (4.57)	.180 (4.57)	.070 (1.78)	.400 (10.16)	.350 (8.89)	.050 (1.27)	.015 (0.38)	.005 (0.13)	.005 (0.13)	.070 (1.78)	--	.105 (2.67)	.025 (0.64)	.420 (10.67)

CASE #	Q	R	S	WT. GRAM
XX112	.015 (0.38)	.180 (4.57)	.020 (0.51)	.15

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

1. Case material: Kovar.
2. Termination Finish: 50 μ inch (1.27 microns) Gold over 50-350 μ inch (1.27-8.89 microns) Nickel plate.
3. Special Tolerances: Termination thickness $\pm .002$ inch.