

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	VSWR (:1)
10.0	53.73	168.77
50.0	41.60	185.95
100.0	36.66	233.22
150.0	34.92	141.35
200.0	34.87	105.71
250.0	35.97	80.35
300.0	38.23	62.12
350.0	41.83	49.72
400.0	47.72	41.96
450.0	57.18	34.97
500.0	52.27	29.38
550.0	49.51	24.68
600.0	50.01	20.21
650.0	50.72	15.88
700.0	43.94	11.80
750.0	33.64	7.76
810.0	25.59	3.40
850.0	9.35	1.55
900.0	3.72	1.20
950.0	2.44	1.14
1000.0	1.88	1.15
1100.0	1.47	1.43
1200.0	1.27	1.47
1300.0	1.07	1.31
1400.0	0.93	1.11
1500.0	0.91	1.20
1600.0	0.99	1.42
1700.0	1.12	1.62
1800.0	1.24	1.72
1900.0	1.32	1.71
2000.0	1.39	1.60
2100.0	1.49	1.45
2200.0	1.77	1.37
2300.0	2.55	1.64
2400.0	4.82	2.85
2500.0	9.79	6.26
2600.0	16.92	12.37
2700.0	25.54	19.76
2800.0	37.08	27.59
2900.0	42.30	35.27
3000.0	38.08	42.51
3100.0	37.13	49.25
3200.0	37.44	55.89
3300.0	38.31	60.19
3400.0	39.47	64.52
3500.0	40.81	68.65
3600.0	42.19	70.77
3700.0	43.64	72.19
3800.0	45.04	74.10
3900.0	46.45	72.82
4000.0	47.71	72.79
4100.0	49.12	71.98
4200.0	50.40	70.12
4300.0	51.81	70.00
4400.0	53.22	67.27
4500.0	54.61	66.32
4600.0	56.94	63.92
4700.0	58.74	60.99
4800.0	53.12	56.13
4900.0	45.37	46.93
5000.0	37.41	30.84