

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
10	63.06	0.07
50	60.50	0.06
100	57.27	0.04
200	52.45	0.02
300	49.06	0.01
400	46.74	0.00
500	44.85	0.00
600	43.41	0.00
700	42.14	0.00
800	41.11	0.01
900	40.17	0.01
1000	39.35	0.00
1500	36.46	0.00
2000	34.93	0.00
2500	34.78	0.03
3000	37.75	0.07
3360	50.53	0.13
3500	50.55	0.15
4000	32.25	0.32
4500	7.45	3.46
5000	1.03	15.43
5050	0.94	17.47
5100	0.86	20.31
5150	0.80	24.36
5200	0.76	31.03
5250	0.72	35.84
5300	0.71	28.00
5350	0.69	23.89
5400	0.69	21.40
5450	0.69	19.95
5500	0.68	19.00
5515	0.68	18.86
5550	0.68	18.37
5600	0.68	18.23
5650	0.67	18.33
5700	0.66	18.58
5750	0.66	19.18
5800	0.66	19.90
5850	0.67	20.37
5900	0.68	20.36
5930	0.70	19.87
6000	0.76	17.69
6500	2.96	4.42
7000	8.12	1.17
7500	13.17	0.65
8000	19.03	0.73
8500	22.00	0.49
8770	23.60	0.38
9000	24.88	0.30
9500	27.10	0.24
10000	28.74	0.19
10500	30.94	0.15
11000	32.94	0.22
11500	34.11	0.38
12000	33.90	0.60
12500	35.85	0.69
13000	42.81	0.68
13500	60.73	0.61
14000	48.21	0.55
14500	50.56	0.57
15000	39.77	0.54
15200	38.14	0.53
15400	37.39	0.51
15600	36.58	0.49
15800	35.46	0.48
16000	34.16	0.50