

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
10	73.63	0.02
55	62.92	0.00
100	59.37	0.00
200	69.27	0.02
300	48.50	0.05
400	38.98	0.09
500	33.17	0.16
600	29.14	0.23
700	26.28	0.32
800	24.47	0.42
900	24.24	0.55
1000	28.91	0.75
1050	32.63	0.94
1077	25.87	1.09
1100	20.80	1.29
1150	12.91	2.07
1200	7.29	4.00
1250	3.78	8.42
1300	2.18	17.34
1350	1.59	35.99
1400	1.36	21.62
1450	1.22	20.01
1488	1.14	20.65
1500	1.12	21.07
1600	0.99	26.24
1700	0.94	22.22
1800	0.94	18.65
1900	0.94	17.82
2000	0.94	19.10
2100	0.95	23.30
2153	0.97	27.30
2200	1.00	32.10
2300	1.13	31.41
2400	1.40	21.84
2500	2.24	11.08
2600	4.82	4.69
2700	9.53	1.98
2800	15.16	1.05
2900	21.08	0.69
2976	25.78	0.54
3100	34.71	0.42
3250	54.25	0.33
3500	39.25	0.24
3750	37.12	0.20
4000	36.39	0.18
4250	35.87	0.17
4500	35.30	0.20
4750	34.56	0.25
5000	33.44	0.30
5250	32.25	0.35
5500	31.47	0.35
5750	31.06	0.34
6000	30.67	0.34
6250	30.33	0.37
6500	30.05	0.38
6750	30.10	0.39
7000	31.32	0.41
7250	22.41	0.84
7500	25.07	0.44
7750	25.44	0.41
8000	25.28	0.40
8250	25.00	0.42
8500	25.58	0.45
8750	26.81	0.33
9000	25.76	0.32
9250	25.50	0.48
9500	26.73	0.28
9750	25.91	0.27
10000	25.25	0.32