

Typical Performance Data

| FREQUENCY (MHz) | INSERTION LOSS (dB) | RETURN LOSS (dB) |
|--------------------|------------------------|---------------------|
| 100 | 96.13 | 0.06 |
| 1000 | 76.71 | 0.26 |
| 5000 | 63.60 | 0.11 |
| 7000 | 61.17 | 0.03 |
| 10000 | 57.87 | 0.20 |
| 12000 | 53.33 | 0.20 |
| 14000 | 45.73 | 0.20 |
| 17100 | 30.59 | 0.14 |
| 18000 | 25.31 | 0.20 |
| 19000 | 18.92 | 0.41 |
| 20000 | 11.48 | 0.88 |
| 21000 | 3.40 | 4.15 |
| 22000 | 0.69 | 28.36 |
| 23000 | 0.61 | 24.31 |
| 24000 | 0.59 | 25.37 |
| 25000 | 0.68 | 16.67 |
| 26000 | 0.71 | 16.17 |
| 27000 | 0.66 | 28.65 |
| 28000 | 0.83 | 16.80 |
| 29000 | 0.97 | 14.67 |
| 30000 | 0.92 | 22.92 |
| 31000 | 1.17 | 16.47 |
| 32000 | 1.93 | 16.47 |
| 34000 | 30.08 | 0.35 |
| 35700 | 49.40 | 0.14 |
| 37000 | 45.72 | 0.23 |
| 38000 | 46.43 | 0.34 |
| 40000 | 48.71 | 0.52 |
| 43000 | 50.85 | 0.34 |
| 46000 | 47.77 | 0.30 |
| 48000 | 45.07 | 0.29 |
| 52000 | 31.99 | 0.72 |
| 55000 | 6.29 | 4.02 |
| 58000 | 12.56 | 1.97 |
| 60000 | 10.07 | 2.81 |