

*Typical Performance Data*

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
10	79.20	0.05
50	67.11	0.05
100	61.12	0.05
200	55.17	0.06
300	51.80	0.06
400	49.55	0.07
500	47.82	0.07
600	46.60	0.07
700	45.72	0.08
800	45.16	0.08
900	44.96	0.08
1000	45.17	0.09
1100	45.99	0.09
1200	47.82	0.11
1300	53.17	0.11
1400	62.74	0.12
1500	46.81	0.13
1600	39.67	0.14
1700	34.26	0.16
1860	26.82	0.22
1900	25.06	0.25
2000	20.51	0.37
2100	15.55	0.67
2200	9.95	1.64
2300	4.56	5.96
2400	2.37	43.37
2410	2.33	30.91
2420	2.30	25.12
2430	2.30	22.16
2440	2.30	20.35
2450	2.32	19.11
2460	2.34	18.19
2470	2.38	17.44
2480	2.43	16.71
2490	2.50	15.91
2500	2.60	14.98
2600	5.49	4.85
2700	11.38	1.53
2800	17.46	0.69
2900	23.17	0.40
3000	29.06	0.27
3200	44.65	0.15
3400	37.31	0.11
3600	35.19	0.08
3800	33.40	0.05
4000	32.25	0.04
4200	31.60	0.04
4400	31.32	0.06
4600	31.23	0.08
4800	31.40	0.11
5000	31.87	0.14
5200	32.57	0.16
5400	33.41	0.19
5600	34.23	0.23
5800	35.23	0.27
6000	36.37	0.30
6200	38.30	0.32
6400	42.47	0.34
6600	50.18	0.34
6800	55.77	0.34
7000	43.88	0.34
7200	38.84	0.34
7400	35.98	0.35
7600	34.72	0.38
7800	34.15	0.43
8000	50.56	0.35