

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
100	111.79	-0.02
500	106.58	-0.02
1000	107.96	0.00
2000	107.75	-0.05
3000	109.71	-0.08
4000	110.46	-0.11
5000	114.59	-0.10
6000	107.36	-0.06
7000	113.26	-0.01
8000	112.30	0.13
9000	110.87	0.19
10000	105.72	0.01
11000	111.94	-0.15
12000	123.35	0.07
12600	123.64	0.31
14000	104.27	0.18
15000	94.87	-0.16
16000	86.26	-0.28
17000	76.21	-0.07
18000	64.74	0.35
19000	51.81	0.38
20000	33.23	-0.07
21000	3.59	9.72
22000	2.00	12.58
22500	1.93	14.32
23000	2.15	9.15
23500	1.80	23.01
24000	1.84	13.83
24500	2.07	12.54
25000	2.03	13.54
25500	1.82	19.52
26000	1.94	15.71
26500	1.96	16.04
27000	2.06	17.81
27500	2.52	10.78
28000	2.66	10.12
29000	4.12	8.46
30000	25.79	1.03
31000	50.98	-0.56
32000	70.21	0.01
33000	89.99	0.98
34000	97.56	1.13
35000	105.02	0.83
36000	99.06	0.16
37000	98.63	-0.40
38000	107.59	0.27
39000	88.46	2.57
40000	82.64	4.41
41000	86.88	2.45
42000	81.42	-0.07
43000	86.85	-0.47
44000	93.14	0.18
45000	85.61	0.89
46000	83.69	1.25
47000	89.10	1.01
48000	90.48	0.17
49000	97.00	-0.60
50000	89.95	-0.88
52000	81.05	0.42
54000	65.78	0.76
56000	86.26	-0.89
58000	78.62	-0.95
60000	78.62	-0.95
62000	78.62	-0.95
64000	78.62	-0.95
66000	78.62	-0.95
67000	78.62	-0.95