

LTCC Bandpass Filter

BFHKI-6751+

<i>Typical Performance Data</i>		
FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
100	97.57	0.06
1000	80.49	0.19
1500	76.29	0.17
2000	74.76	0.13
2500	73.59	0.10
3000	73.94	0.10
3500	76.38	0.14
4000	83.55	0.21
4500	74.37	0.31
5000	48.40	0.52
5500	4.58	11.01
5900	2.69	17.65
6000	2.58	22.86
6500	2.80	19.64
6900	3.32	31.88
7000	3.58	23.96
7500	12.37	8.27
8000	69.45	0.87
8500	67.78	0.52
9000	71.12	0.41
9200	73.08	0.37
9500	75.51	0.34
10000	76.55	0.30
11000	70.20	0.35
12000	63.13	0.44
13000	63.80	0.40
14000	54.59	0.33
15000	52.75	0.41
16000	55.69	0.45
17000	60.41	0.34
18000	52.40	0.30
19000	45.62	0.46
20000	39.07	0.62

