

*Typical Performance Data*

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
3	0.38	12.71
5	0.21	16.98
7	0.16	19.85
9	0.14	22.03
10	0.14	23.03
16	0.13	27.72
22	0.15	31.75
30	0.18	36.03
34	0.19	37.58
46	0.20	42.61
60	0.21	48.98
72	0.22	48.42
86	0.22	44.08
100	0.23	40.07
104	0.23	38.98
124	0.24	35.63
146	0.26	32.77
168	0.27	30.98
188	0.28	29.44
210	0.30	28.05
232	0.31	26.76
254	0.33	25.60
274	0.34	24.71
296	0.36	23.80
318	0.38	22.90
340	0.39	22.22
360	0.40	21.50
382	0.43	20.78
404	0.45	20.09
426	0.48	19.47
446	0.50	18.89
468	0.52	18.23
490	0.55	17.56
512	0.58	16.91
520	0.60	16.65
556	0.67	15.47
592	0.77	14.15