

RF Transformer

TCW2-362+

Typical Performance Data

FREQUENCY MHz	AVERAGE INSERTION LOSS (dB)	INPUT RETURN LOSS (dB)	AMPLITUDE UNBALANCE (dB)	PHASE UNBALANCE (deg.)
2150	3.75	23.62	0.57	3.91
2180	3.75	23.00	0.55	3.73
2210	3.76	22.32	0.52	3.48
2240	3.77	21.39	0.50	3.21
2270	3.78	20.76	0.48	3.00
2300	3.78	20.42	0.46	2.80
2330	3.79	19.81	0.43	2.44
2360	3.79	19.14	0.41	2.25
2390	3.80	18.80	0.40	1.98
2420	3.81	18.48	0.37	1.77
2450	3.82	17.91	0.36	1.51
2480	3.83	17.54	0.34	1.14
2510	3.84	17.32	0.32	0.91
2540	3.85	17.00	0.30	0.64
2570	3.85	16.59	0.28	0.38
2600	3.86	16.29	0.27	0.11
2630	3.87	16.20	0.26	0.09
2660	3.88	15.96	0.26	0.51
2690	3.88	15.58	0.23	0.92
2720	3.89	15.41	0.21	1.08
2750	3.89	15.37	0.21	1.40
2780	3.90	15.10	0.19	1.73
2810	3.91	14.84	0.19	2.08
2840	3.91	14.81	0.18	2.38
2870	3.92	14.75	0.16	2.72
2900	3.92	14.54	0.14	3.00
2930	3.93	14.36	0.15	3.32
2960	3.93	14.39	0.13	3.68
2990	3.94	14.36	0.13	3.94
3020	3.95	14.17	0.13	4.38
3050	3.95	14.07	0.12	4.60
3080	3.95	14.19	0.13	4.90
3110	3.95	14.18	0.12	5.32
3140	3.96	13.98	0.11	5.60
3170	3.96	14.04	0.12	5.86
3200	3.96	14.19	0.13	6.23
3230	3.97	14.17	0.12	6.62
3260	3.97	14.07	0.13	6.81
3290	3.97	14.23	0.15	7.16
3320	3.97	14.44	0.14	7.45
3350	3.97	14.42	0.18	7.81
3380	3.97	14.42	0.18	8.21
3410	3.97	14.64	0.19	8.42
3440	3.97	14.94	0.21	8.78
3470	3.97	14.95	0.23	9.07
3500	3.97	15.05	0.27	9.43
3530	3.97	15.40	0.28	9.81
3560	3.97	15.60	0.30	10.21
3590	3.98	15.65	0.32	10.46
3600	3.97	15.70	0.33	10.53

