

Typical Performance Data

FREQUENCY	INSERTION LOSS	RETURN LOSS
(MHz)	(dB)	(dB)
0.3	67.55	0.01
1.0	57.63	0.00
3.0	47.89	0.00
10.0	37.53	0.00
30.0	28.64	0.01
70.0	23.94	0.06
100.0	23.40	0.08
300.0	29.47	0.16
500.0	38.57	0.19
700.0	48.02	0.21
1000.0	35.80	0.25
1200.0	34.76	0.28
1300.0	37.00	0.31
1400.0	52.82	0.37
1450.0	38.04	0.42
1500.0	29.50	0.49
1600.0	18.05	0.84
1650.0	13.00	1.35
1700.0	8.24	2.66
1750.0	4.41	6.20
1800.0	2.50	12.96
1850.0	2.02	12.92
1875.0	1.95	11.99
1900.0	1.88	11.83
1950.0	1.72	14.07
1975.0	1.65	17.21
2000.0	1.62	23.39
2020.0	1.65	24.59
2040.0	1.76	17.88
2060.0	1.94	13.43
2080.0	2.21	10.43
2200.0	5.25	3.09
2400.0	10.96	0.90
2600.0	15.21	0.48
2800.0	18.55	0.36
2900.0	20.02	0.33
3000.0	21.38	0.30
3200.0	23.94	0.29
3400.0	26.67	0.29
3600.0	29.39	0.30
3800.0	32.78	0.32
4000.0	37.23	0.33
4200.0	44.12	0.34
4400.0	52.63	0.36
4600.0	42.92	0.38
4800.0	39.04	0.39
5000.0	37.06	0.40
5200.0	36.51	0.42
5400.0	38.52	0.45
5500.0	40.81	0.49
5600.0	39.89	0.53
5700.0	32.47	0.62
5800.0	24.79	0.89
5900.0	17.91	1.63
6000.0	14.54	2.01