

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
60.0	82.52	0.10
60.9	85.71	0.16
62.0	88.94	0.08
63.0	87.53	0.12
63.9	84.03	0.10
65.0	90.18	0.08
66.0	89.28	0.13
66.9	94.15	0.07
68.0	78.43	0.14
68.3	89.71	0.14
68.6	93.10	0.17
68.9	73.69	0.15
69.2	68.98	0.20
69.5	60.12	0.18
69.8	47.81	0.28
70.1	31.99	0.44
70.4	9.92	1.78
70.7	1.40	14.50
71.0	0.90	26.10
71.3	0.77	28.89
71.6	0.70	31.36
71.9	0.67	22.70
72.2	0.61	22.89
72.5	0.54	29.06
72.8	0.54	21.13
73.1	0.53	27.29
73.4	0.52	26.23
73.7	0.51	22.52
74.0	0.48	39.27
74.3	0.52	19.33
74.6	0.53	17.49
74.9	0.47	27.22
75.2	0.49	24.36
75.5	0.47	26.78
75.8	0.49	22.61
76.1	0.58	19.63
76.4	0.65	25.90
77.1	24.52	0.32
77.9	48.55	0.15
79.1	73.01	0.05
79.8	79.01	0.09
81.0	79.78	0.08
81.8	77.64	0.08
83.0	80.58	0.14
84.2	78.22	0.09
85.4	77.39	0.13
86.6	84.88	0.02
87.8	79.98	0.11
89.0	83.41	0.07
90.0	83.79	0.04