

Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	VSWR (:1)
10	15.01	1.19
50	14.99	1.19
100	14.99	1.19
200	14.99	1.18
300	14.99	1.18
400	15.00	1.18
500	15.00	1.18
1000	15.01	1.17
1500	14.99	1.15
2000	14.98	1.13
2500	14.95	1.11
3000	14.94	1.08
3500	14.92	1.06
4000	14.93	1.04
4500	14.92	1.03
5000	14.93	1.04
5500	14.93	1.08
6000	14.94	1.12
6500	14.95	1.15
7000	14.97	1.16
7500	14.96	1.16
8000	14.97	1.14
8500	14.97	1.11
9000	14.97	1.10
9500	14.97	1.10
10000	14.98	1.11
10500	14.98	1.13
11000	14.98	1.14
11500	14.98	1.15
12000	14.98	1.16
12500	14.98	1.16
13000	14.99	1.16
13500	14.99	1.16
14000	15.00	1.18
14500	15.01	1.21
15000	15.03	1.24
15500	15.04	1.27
16000	15.04	1.26
16500	15.02	1.25
17000	15.00	1.22
17500	14.97	1.19
18000	14.95	1.18