

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS Control @ 0V/-5V (dB) IN-OUT , "ON"	ISOLATION Control @ 0V/-5V (dB) IN-OUT , "OFF"	VSWR (:1)		
			IN	OUT , "ON"	OUT , "OFF"
3	0.54	83.44	1.12	1.12	16.46
5	0.54	83.46	1.12	1.12	16.21
10	0.54	81.44	1.12	1.12	16.21
20	0.61	76.29	1.12	1.12	16.04
50	0.59	69.27	1.12	1.12	15.37
100	0.62	66.59	1.12	1.12	14.63
200	0.65	61.43	1.12	1.12	14.00
500	0.70	53.61	1.13	1.13	12.83
912	0.75	47.64	1.14	1.15	11.86
1000	0.76	46.91	1.14	1.16	11.79
1581	0.92	41.27	1.22	1.20	11.85
2107	0.92	37.77	1.36	1.21	11.91
2370	0.88	37.33	1.37	1.26	9.64
2490	1.01	36.86	1.41	1.34	9.98
2753	1.17	35.65	1.51	1.42	9.70
3279	1.15	33.10	1.53	1.39	13.14
3805	1.16	33.46	1.50	1.35	13.37
4331	0.87	31.99	1.31	1.24	15.41
4474	0.70	32.16	1.23	1.23	17.84
4600	1.08	32.78	1.13	1.16	14.40