


### Outline Dimensions



#### MA1628 SERIES

2.92mm K-MALE (CONN-1)

2.92mm K-MALE (CONN-2)

CASE STYLE #	A		B	C	D	E	T		WEIGHT GRAMS
	FEET	METERS					INCH	MM	
MA1628-1.5	1.50	.46	.40 (10.16)	.312 (7.92)	.40 (10.16)	.312 (7.92)	+.50/-0	+12.7/-0	75
MA1628-2	2.00	.61					+.50/-0	+12.7/-0	91
MA1628-3.28	3.28	1.00					+.79/-0	+20.0/-0	130
MA1628-4	4.00	1.22					+.96/-0	+24.4/-0	152
MA1628-6.56	6.56	2.00					+1.57/-0	+40.0/-0	231

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl.  $\pm .03$ ; 3Pl.  $\pm .015$

#### Note:

1. Low Loss Armored Flexible Cable.