



\* OVERALL CONNECTOR OR CABLE & BOOT DIM  
[CONNECTOR SHAPE MAY VARY]

### RL2850 SERIES 2.4 MM MALE (CONN)

CASE STYLE #	A		B	C	D	E	F	T		WT. (GRAMS)
	FEET	METERS						INCH	MM	
RL2850-2	2.00	.61	.36 [9.25]	.315 [8.00]	.36 [9.25]	.315 [8.00]	.142 [3.60]	+.08	+2.0	47.0
RL2850-3	3.00	.91						-0	-0	

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2 Pl.±.03; 3 Pl. ±.015

#### Note:

1. Low Loss Flexible (T50) Cable.