

*Typical Performance Data*

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
10.0	0.03	36.33	36.39
50.0	0.04	44.50	46.13
100.0	0.07	42.21	43.10
200.0	0.10	40.80	41.17
300.0	0.12	44.50	44.40
400.0	0.13	52.73	51.60
500.0	0.15	42.06	40.66
600.0	0.17	39.84	38.62
700.0	0.18	45.74	45.09
800.0	0.19	45.46	44.93
900.0	0.21	39.64	38.67
1000.0	0.22	42.36	41.58
1100.0	0.23	53.12	51.07
1250.0	0.25	39.48	40.22
1500.0	0.27	44.18	42.66
1750.0	0.29	48.69	45.70
2000.0	0.32	38.23	38.21
2001.0	0.32	38.23	38.24
2250.0	0.34	44.50	45.09
2500.0	0.36	47.22	43.04
2750.0	0.38	42.05	36.12
3000.0	0.40	42.53	41.44
3250.0	0.41	41.04	42.29
3500.0	0.43	41.60	40.99
3750.0	0.45	39.62	43.25
4000.0	0.46	38.16	35.97
4250.0	0.47	46.76	35.34
4500.0	0.49	45.15	37.56
5000.0	0.52	36.71	47.13
5500.0	0.56	52.03	39.00
6000.0	0.59	35.46	32.41
6500.0	0.62	38.29	33.58
7000.0	0.66	37.06	34.47
7500.0	0.68	30.50	31.72
8000.0	0.72	44.39	37.66
8500.0	0.73	28.06	27.70
9000.0	0.75	37.47	35.70
9500.0	0.78	29.63	28.13
10000.0	0.81	27.06	27.43
10500.0	0.80	39.60	33.37
11000.0	0.89	25.32	25.47
11500.0	0.87	30.37	30.79
12000.0	0.94	27.29	26.69
12500.0	0.92	27.16	26.53
13000.0	0.94	30.36	35.80
13500.0	0.96	24.68	23.87
14000.0	0.95	30.99	25.05
14500.0	1.03	27.84	26.54
15000.0	1.01	30.58	28.21
15500.0	1.06	36.60	31.96
16000.0	1.04	26.11	26.76
16500.0	1.14	34.51	42.63
17000.0	1.11	24.95	24.30
17500.0	1.16	28.66	27.35
18000.0	1.14	29.14	28.35