

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	2.92mm-MALE 1 RETURN LOSS (dB)	2.92mm-MALE 2 RETURN LOSS (dB)
10	0.03	53.4	49.1
50	0.02	49.6	47.2
100	0.03	46.4	44.4
1000	0.13	40.6	40.9
2000	0.19	49.2	48.9
3000	0.23	34.4	33.8
4000	0.26	36.7	36.1
5000	0.29	35.8	35.8
6000	0.32	27.7	27.8
7000	0.34	26.8	26.5
8000	0.35	32.1	32.6
9000	0.37	32.7	32.8
10000	0.40	28.7	28.9
11000	0.42	32.1	32.7
12000	0.43	46.6	40.7
13000	0.45	33.6	33.1
14000	0.47	41.2	35.8
15000	0.49	36.1	37.6
16000	0.51	30.4	29.9
17000	0.53	33.1	31.3
18000	0.55	32.2	32.7
19000	0.58	35.9	36.9
20000	0.60	34.5	36.3
21000	0.62	33.0	32.0
22000	0.65	33.0	33.4
23000	0.67	38.4	51.8
24000	0.69	35.1	33.4
25000	0.72	32.0	32.7
26000	0.74	35.4	36.4
27000	0.76	38.6	37.4
28000	0.79	36.1	34.4
29000	0.81	32.0	31.7
30000	0.82	33.8	35.4
31000	0.85	37.4	34.7
32000	0.86	35.3	36.6
33000	0.88	29.4	32.5
34000	0.91	29.2	27.6
35000	0.93	32.9	37.1
36000	0.95	31.2	33.3
37000	0.98	27.7	26.3
38000	1.01	29.4	30.4
39000	1.03	34.4	35.5
40000	1.05	29.3	29.6