

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
10	0.06	47.1	46.0
50	0.05	33.8	33.7
100	0.07	33.4	33.5
200	0.11	37.3	36.6
300	0.14	39.7	39.9
400	0.16	32.8	32.9
500	0.18	51.6	48.8
500	0.18	51.6	48.8
1000	0.26	42.3	43.7
1500	0.33	36.0	36.5
2000	0.39	35.5	35.8
2500	0.44	32.4	32.9
3000	0.48	34.9	34.8
3500	0.53	31.4	31.4
4000	0.57	31.7	32.0
4500	0.61	32.2	32.7
5000	0.65	32.1	33.6
5500	0.69	31.8	31.7
6000	0.72	34.5	35.0
6500	0.75	38.6	40.9
7000	0.79	39.6	36.7
7500	0.82	46.3	49.2
8000	0.85	57.6	43.7
8500	0.88	44.0	40.5
9000	0.91	43.0	40.4
9500	0.94	36.8	36.6
10000	0.97	32.6	33.6
10500	1.00	32.4	32.9
11000	1.03	29.7	29.5
11500	1.08	23.6	23.5
12000	1.10	26.6	26.7
12500	1.12	28.9	29.9
13000	1.14	31.8	32.9
13500	1.17	30.9	31.4
14000	1.19	38.2	34.5
14500	1.22	43.1	41.4
15000	1.24	32.1	30.5
15500	1.28	32.0	29.5
16000	1.30	39.4	37.9
16500	1.32	33.8	32.7
17000	1.35	33.9	33.5
17500	1.38	28.6	28.4
18000	1.40	31.8	34.8