

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-FEMALE BULKHEAD RETURN LOSS (dB)	SMA-MALE RETURN LOSS (dB)
10	0.00	58.9	58.7
100	0.02	43.7	43.9
200	0.03	38.9	39.1
300	0.03	36.6	37.2
500	0.04	35.3	36.5
600	0.05	36.1	37.3
800	0.06	39.6	40.8
900	0.06	42.8	44.4
1000	0.06	48.0	49.0
1200	0.07	48.4	44.1
1400	0.07	40.9	39.9
1600	0.08	38.5	39.3
1800	0.08	39.0	40.9
2000	0.09	42.0	42.7
2200	0.09	48.5	42.5
2400	0.09	46.2	41.3
2600	0.10	42.1	41.3
2800	0.10	40.7	43.2
3000	0.10	41.9	43.4
3500	0.11	38.7	40.2
4000	0.12	42.8	46.7
4500	0.13	33.0	35.2
5000	0.13	34.5	39.8
5500	0.14	34.9	39.0
6000	0.14	32.1	36.2
6500	0.15	41.9	48.4
7000	0.15	33.9	36.8
7500	0.16	39.8	46.8
8000	0.16	32.9	39.4
8500	0.17	51.1	43.2
9000	0.17	34.0	38.1
9500	0.18	36.2	37.7
10000	0.17	30.8	43.8
10500	0.19	35.5	35.3
11000	0.18	33.7	45.8
11500	0.20	32.1	32.5
12000	0.19	25.2	30.2
12500	0.20	29.5	31.6
13000	0.20	28.6	33.2
13500	0.21	30.6	34.7
14000	0.19	29.4	32.2
14500	0.22	31.8	37.4
15000	0.20	30.0	32.9
15500	0.22	30.7	35.2
16000	0.22	30.0	32.1
16500	0.23	28.5	30.8
17000	0.23	34.4	36.2
17500	0.24	33.1	33.7
18000	0.25	29.7	30.6