

Low Pass Filter

BBFCG2-252+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
10.00	77.60	0.06
1000.0	38.04	0.10
1360.0	56.37	0.34
1550.0	37.64	1.39
1600.0	22.79	3.71
2300.0	0.83	24.74
2490.0	0.90	25.90
2690.0	1.27	22.97
3000.0	10.37	3.08
3320.0	50.12	0.40
4000.0	33.54	0.11
4500.0	41.76	0.01
5000.0	38.17	0.01
5500.0	48.61	0.00
6000.0	47.18	0.00
6500.0	44.42	0.09
7000.0	41.91	0.31
7500.0	40.05	0.60
8000.0	38.25	0.93
8500.0	37.33	1.30
9000.0	47.39	0.73
9500.0	41.14	0.98
10000.0	40.39	2.95

