

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
100	91.68	0.06
1000	71.93	0.23
5000	57.77	0.09
10000	52.33	0.09
15000	46.60	0.11
18000	42.11	0.07
24000	34.43	0.14
27000	28.36	0.11
29000	23.73	0.25
31000	18.05	0.36
33000	10.36	0.95
35000	2.63	5.09
36500	0.74	20.53
37000	0.75	18.45
38000	0.77	15.70
39000	0.76	16.76
40000	0.75	19.11
41000	0.72	22.64
42000	0.74	20.10
43000	0.76	18.54
44000	0.72	19.04
45000	0.72	19.95
46000	0.82	20.78
47000	0.90	20.43
48000	0.93	18.16
49000	1.07	15.19
50000	1.28	15.16
52000	4.60	4.32
54000	18.45	0.72
56000	39.08	0.66
57300	48.90	0.87
59000	42.96	0.95
63000	20.51	3.19
65000	16.60	5.41
67000	23.84	2.65