

# Test Cable, SMA-Male/SMA-Male CBL-25FT-SMSM+

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
100.00	0.82	46.76	46.09
416.67	1.75	32.12	32.38
733.33	2.37	34.02	34.75
1050.00	2.89	27.14	27.46
1366.67	3.32	32.92	32.00
1683.33	3.72	27.84	28.88
2000.00	4.08	27.59	28.54
2666.67	4.79	35.43	35.54
3333.33	5.42	38.83	39.04
4000.00	6.02	35.83	39.69
4666.67	6.56	33.04	33.44
5333.33	7.08	31.57	35.13
6000.00	7.56	32.86	33.38
7000.00	8.25	40.05	35.69
8000.00	8.93	39.67	33.38
9000.00	9.58	31.28	28.67
10000.00	10.14	30.89	31.05
11000.00	10.75	41.80	28.49
12000.00	11.35	27.81	26.00
12857.14	11.75	28.02	28.11
13714.29	12.18	27.56	26.04
14571.43	12.61	28.64	30.75
15428.57	13.05	26.32	26.68
16285.71	13.56	29.37	27.77
17142.86	14.11	31.82	30.43
18000.00	14.64	27.11	29.48