

Typical Performance Data

| FREQUENCY (MHz) | INSERTION LOSS (dB) | F-MALE 1 RETURN LOSS (dB) | F-MALE 2 RETURN LOSS (dB) |
|--------------------|------------------------|---------------------------------|---------------------------------|
| 50.0 | 0.06 | 38.9 | 38.3 |
| 200.0 | 0.13 | 42.2 | 43.3 |
| 350.0 | 0.18 | 42.8 | 49.3 |
| 500.0 | 0.22 | 43.3 | 44.0 |
| 500.3 | 0.22 | 43.4 | 43.8 |
| 500.7 | 0.22 | 43.5 | 44.0 |
| 501.0 | 0.22 | 43.3 | 44.1 |
| 667.3 | 0.26 | 41.4 | 40.0 |
| 833.7 | 0.29 | 43.0 | 41.4 |
| 1000.0 | 0.32 | 47.5 | 43.3 |
| 1334.0 | 0.37 | 46.3 | 37.6 |
| 1667.0 | 0.39 | 37.9 | 39.9 |
| 2000.0 | 0.45 | 37.4 | 43.8 |
| 2143.7 | 0.45 | 38.1 | 36.2 |
| 2286.4 | 0.50 | 38.4 | 33.4 |
| 2429.1 | 0.58 | 39.3 | 29.7 |
| 2571.9 | 0.59 | 36.0 | 27.6 |
| 2714.6 | 0.59 | 34.0 | 25.8 |
| 2857.3 | 0.55 | 33.2 | 26.3 |
| 3000.0 | 0.56 | 31.3 | 31.0 |