

*Typical Performance Data*

FREQUENCY (MHz)	INSERTION LOSS (dB)	2.92mm-MALE 1 RETURN LOSS (dB)	2.92mm-MALE 2 RETURN LOSS (dB)
10	0.02	50.34	48.48
50	0.05	42.43	42.35
100	0.07	37.29	36.93
200	0.11	32.61	32.45
300	0.14	33.87	33.70
400	0.16	40.02	41.91
500	0.18	38.93	39.58
600	0.20	34.70	34.72
700	0.21	37.99	37.41
800	0.23	42.43	41.39
900	0.24	35.49	34.63
1000	0.26	33.03	32.96
1500	0.31	38.62	37.10
2000	0.35	37.54	36.39
2500	0.39	32.85	31.76
3000	0.41	43.21	42.25
3500	0.44	33.17	33.93
4000	0.47	37.43	37.45
4500	0.50	34.61	36.14
5000	0.54	31.92	31.59
5500	0.56	39.25	39.57
6000	0.60	29.66	29.74
6500	0.62	38.29	37.64
7000	0.64	30.49	31.00
7500	0.67	28.78	28.66
8000	0.68	39.98	40.06
9000	0.72	32.99	32.69
10000	0.76	25.64	25.49
11000	0.81	23.68	23.61
12000	0.83	27.38	26.73
13000	0.86	37.36	34.10
14000	0.89	28.75	27.61
15000	0.94	24.10	23.60
16000	0.97	22.79	22.35
17000	0.99	24.64	23.46
18000	1.02	32.98	29.92
20000	1.10	26.58	26.67
22000	1.16	31.79	33.58
23000	1.20	29.54	29.05
24000	1.24	26.90	25.18
26500	1.30	33.63	31.33
28000	1.34	37.46	39.46
30000	1.40	35.09	32.71
32000	1.45	24.59	23.05
33000	1.47	26.30	23.57
34000	1.50	34.84	25.31
36000	1.58	28.26	28.30
38000	1.66	25.43	26.67
40000	1.73	31.74	34.98