

*Typical Performance Data*

FREQUENCY (MHz)	INSERTION LOSS (dB)	2.92mm-MALE RETURN LOSS (dB)	2.4mm-MALE RETURN LOSS (dB)
100	0.08	37.26	37.11
1000	0.25	34.50	33.11
2000	0.34	45.83	41.67
3000	0.41	30.82	29.42
4000	0.47	26.10	25.88
5000	0.52	29.11	28.09
6000	0.56	41.15	33.00
7000	0.59	35.32	34.08
8000	0.63	32.01	30.03
9000	0.67	32.80	32.33
10000	0.69	36.24	36.95
11000	0.74	25.37	25.09
12000	0.77	26.93	26.21
13000	0.78	35.01	32.45
14000	0.82	25.04	24.97
15000	0.85	25.68	24.21
16000	0.86	32.20	29.03
17000	0.89	27.23	26.60
18000	0.92	29.27	26.70
19000	0.95	35.75	31.65
20000	0.97	29.17	30.46
21000	1.00	31.52	28.81
22000	1.03	35.94	37.62
23000	1.07	27.66	27.05
24000	1.10	31.57	30.33
25000	1.12	32.60	33.53
26000	1.16	28.27	27.13
27000	1.19	29.01	31.39
28000	1.21	37.14	38.31
29000	1.24	31.56	29.72
30000	1.26	31.39	29.46
31000	1.28	32.12	29.72
32000	1.31	29.87	27.50
33000	1.33	29.30	27.71
34000	1.36	25.51	23.83
35000	1.39	24.93	22.82
36000	1.40	30.09	26.21
37000	1.44	22.48	21.51
38000	1.47	22.58	21.00
39000	1.46	32.68	29.25
40000	1.52	21.59	19.95