

*Typical Performance Data*

FREQUENCY (GHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
0.01	0.01	54.39	56.16
0.02	0.02	53.80	52.19
0.03	0.02	51.96	51.44
0.04	0.02	50.33	49.80
0.05	0.03	48.11	48.58
0.06	0.03	47.27	47.10
0.07	0.03	45.77	45.94
0.08	0.04	44.81	44.73
0.09	0.04	43.36	43.58
0.10	0.04	42.84	42.49
0.20	0.07	36.12	36.27
0.30	0.09	33.77	34.01
0.40	0.10	35.92	36.01
0.50	0.12	43.75	42.07
1.00	0.17	31.02	30.91
2.00	0.23	34.38	35.19
3.00	0.28	27.66	28.23
3.90	0.31	41.24	49.01
4.80	0.34	39.75	44.17
5.70	0.36	43.74	44.01
6.60	0.39	30.48	30.15
7.50	0.42	31.93	31.59
8.40	0.44	28.15	28.04
9.30	0.47	27.98	28.00
10.20	0.49	31.45	31.42
11.10	0.51	28.95	29.11
12.00	0.53	39.64	45.52
12.90	0.55	32.86	33.30
13.80	0.58	28.91	28.56
14.70	0.59	44.88	47.58
15.60	0.64	23.47	23.18
16.50	0.65	29.40	28.94
17.40	0.68	23.45	22.99
18.30	0.70	25.68	25.32
19.20	0.73	26.21	26.59
20.10	0.75	27.99	27.39
21.00	0.77	26.65	45.77
21.90	0.80	40.97	34.19
22.80	0.83	24.34	30.86
23.70	0.90	23.34	22.96
24.60	0.90	25.40	30.25
25.50	0.99	20.26	19.98
26.40	0.96	31.10	32.42
27.30	1.01	21.58	21.34
28.20	1.01	43.15	33.29