

Test Cable, SMA-Male/SMA-Male

FLC-4FT-SMSM+

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	SMA-MALE 1 VSWR (:1)	SMA-MALE 2 VSWR (:1)
0.1	0.20	1.01	1.02
0.5	0.38	1.03	1.03
1.0	0.53	1.05	1.06
1.5	0.66	1.05	1.07
2.0	0.77	1.07	1.08
2.5	0.87	1.07	1.08
3.0	0.96	1.06	1.07
3.5	1.03	1.06	1.06
4.0	1.10	1.04	1.04
4.5	1.17	1.04	1.04
5.0	1.23	1.04	1.03
5.5	1.30	1.05	1.04
6.0	1.36	1.06	1.06
6.5	1.42	1.06	1.07
7.0	1.49	1.09	1.08
7.5	1.56	1.11	1.10
8.0	1.62	1.12	1.10
8.5	1.64	1.13	1.11
9.0	1.70	1.14	1.12
9.5	1.75	1.15	1.12
10.0	1.73	1.15	1.13
10.5	1.80	1.14	1.13
11.0	1.89	1.13	1.13
11.5	1.89	1.12	1.12
12.0	1.94	1.10	1.11
12.5	2.03	1.09	1.10
13.0	2.08	1.09	1.09
13.5	2.11	1.10	1.09
14.0	2.16	1.09	1.09
14.5	2.29	1.11	1.10
15.0	2.33	1.13	1.10
15.5	2.34	1.13	1.12
16.0	2.48	1.15	1.13
16.5	2.54	1.18	1.17
17.0	2.52	1.20	1.17
17.5	2.64	1.26	1.20
18.0	2.79	1.27	1.21
18.5	2.80	1.27	1.21
19.0	2.87	1.30	1.22
19.5	2.90	1.29	1.19
20.0	2.95	1.26	1.19
20.5	2.98	1.23	1.19
21.0	2.88	1.22	1.19
21.5	2.89	1.18	1.19
22.0	2.94	1.18	1.16
22.5	2.92	1.20	1.14
23.0	2.91	1.22	1.14
23.5	3.08	1.18	1.12
24.0	3.23	1.15	1.10
24.5	3.19	1.15	1.11
25.0	3.21	1.16	1.14
25.5	3.25	1.12	1.17
26.0	3.33	1.16	1.20

