

Termination 50 Ω , N-TYPE

KARN-50-18+

Typical Performance Data

| FREQUENCY (MHz) | RETURN LOSS (dB) |
|--------------------|---------------------|
| 100 | 50.21 |
| 1000 | 44.44 |
| 2000 | 41.16 |
| 4000 | 41.02 |
| 6000 | 42.43 |
| 8000 | 32.99 |
| 10000 | 25.82 |
| 12000 | 23.41 |
| 14000 | 24.96 |
| 16000 | 30.24 |
| 18000 | 22.88 |