

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	N-FEMALE VSWR (:1)	N-MALE VSWR (:1)
10	0.00	1.00	1.00
100	0.00	1.00	1.00
200	0.01	1.00	1.00
300	0.01	1.01	1.00
400	0.01	1.01	1.00
500	0.01	1.01	1.01
600	0.01	1.01	1.00
700	0.01	1.01	1.01
800	0.01	1.01	1.00
900	0.01	1.01	1.00
1000	0.01	1.01	1.00
1200	0.02	1.01	1.00
1400	0.02	1.01	1.00
1600	0.02	1.01	1.01
1800	0.02	1.01	1.01
2000	0.02	1.01	1.01
2200	0.02	1.01	1.01
2400	0.03	1.02	1.01
2600	0.03	1.02	1.01
2800	0.03	1.02	1.01
3000	0.03	1.02	1.01
3200	0.03	1.02	1.01
3400	0.03	1.02	1.01
3600	0.03	1.02	1.02
3800	0.03	1.02	1.02
4000	0.04	1.02	1.02
4500	0.04	1.03	1.03
5000	0.04	1.03	1.03
5500	0.04	1.03	1.03
6000	0.04	1.03	1.03
6500	0.06	1.04	1.04
7000	0.05	1.05	1.02
7500	0.06	1.06	1.02
8000	0.06	1.06	1.04
8500	0.07	1.06	1.07
9000	0.08	1.07	1.07
9500	0.09	1.08	1.06
10000	0.10	1.08	1.06
10500	0.12	1.06	1.06
11000	0.13	1.03	1.05