

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	N-MALE 1 VSWR (:1)	N-MALE 2 VSWR (:1)
10	0.00	1.01	1.00
40	0.01	1.00	1.00
70	0.01	1.00	1.00
100	0.01	1.00	1.00
150	0.01	1.00	1.00
200	0.02	1.01	1.01
250	0.02	1.01	1.01
300	0.02	1.01	1.01
350	0.03	1.01	1.01
400	0.03	1.01	1.01
450	0.03	1.01	1.01
500	0.03	1.01	1.01
550	0.03	1.01	1.01
600	0.03	1.01	1.01
700	0.03	1.01	1.01
800	0.02	1.01	1.01
900	0.04	1.00	1.02
1000	0.06	1.01	1.02
1100	0.07	1.01	1.02
1200	0.08	1.01	1.02
1300	0.08	1.01	1.01
1400	0.07	1.01	1.01
1500	0.07	1.01	1.01
1600	0.07	1.02	1.01
1700	0.07	1.02	1.01
1800	0.08	1.02	1.01
1900	0.08	1.02	1.01
2000	0.08	1.02	1.01
2100	0.08	1.01	1.01
2200	0.07	1.01	1.01
2300	0.07	1.01	1.01
2400	0.06	1.01	1.01
2500	0.06	1.01	1.01
2600	0.05	1.01	1.01
3000	0.05	1.02	1.02
3500	0.05	1.03	1.03
4000	0.06	1.03	1.03
4500	0.07	1.03	1.04
5000	0.07	1.04	1.04
5500	0.08	1.04	1.05
6000	0.08	1.05	1.05