

Typical Performance Data

FREQ.	INSERTION LOSS	SMA-MALE REVERSE POLARITY RETURN LOSS	SMA-MALE RETURN LOSS
(GHz)	(dB)	(dB)	(dB)
0.01	0.00	65.54	61.99
0.05	0.01	51.22	52.38
0.10	0.02	48.26	48.37
0.20	0.03	44.44	45.03
0.30	0.05	42.37	42.73
0.40	0.05	41.69	41.54
0.50	0.06	41.09	40.89
0.60	0.07	40.98	40.16
0.70	0.07	40.87	39.76
0.80	0.08	40.83	39.33
0.90	0.08	40.98	38.94
1.00	0.09	41.11	38.72
1.10	0.08	41.10	38.36
1.20	0.09	41.25	38.15
1.30	0.09	41.06	38.02
1.40	0.09	40.86	37.89
1.50	0.10	40.37	37.70
1.60	0.10	40.03	37.62
1.70	0.10	39.52	37.40
1.80	0.11	39.14	37.28
1.90	0.10	38.65	37.21
2.00	0.11	38.28	36.93
2.20	0.11	37.27	36.68
2.40	0.11	36.70	36.59
2.60	0.12	36.39	36.37
2.80	0.12	36.37	36.27
3.00	0.13	36.50	36.11
3.20	0.13	36.81	36.10
3.40	0.13	37.46	36.18
3.60	0.13	38.47	36.29
3.80	0.13	39.68	36.64
4.00	0.14	41.67	36.81
4.20	0.14	44.35	37.03
4.40	0.14	46.25	36.90
4.60	0.14	43.54	36.03
4.80	0.14	40.14	35.02
5.00	0.15	36.44	33.49
5.20	0.15	33.29	31.65
5.40	0.15	30.59	30.50
5.60	0.16	28.88	28.92
5.80	0.16	26.99	27.67
6.00	0.16	25.61	26.77
6.20	0.17	24.38	25.79
6.40	0.17	23.31	25.03
6.60	0.17	22.60	24.45
6.80	0.17	21.94	23.94
7.00	0.18	21.42	23.40
7.20	0.18	21.08	23.09
7.40	0.18	20.83	22.67
7.60	0.18	20.65	22.40
7.80	0.18	20.69	22.22
8.00	0.19	20.86	22.12
8.50	0.19	21.67	21.75
9.00	0.20	22.65	21.77
9.50	0.19	23.46	21.66
10.00	0.20	23.20	21.39
10.50	0.22	21.68	20.58
11.00	0.23	20.19	19.97
11.50	0.24	19.98	19.91
12.00	0.23	20.54	20.44