

## Typical Performance Data

| FREQUENCY<br>(MHz) | INSERTION<br>LOSS<br>(dB) | RETURN<br>LOSS<br>(dB) |
|--------------------|---------------------------|------------------------|
| 0.02               | 1.24                      | 11.77                  |
| 0.13               | 0.21                      | 26.45                  |
| 1.15               | 0.12                      | 37.26                  |
| 47.47              | 0.40                      | 19.27                  |
| 111.99             | 0.66                      | 14.92                  |
| 147.83             | 0.74                      | 14.64                  |
| 175.75             | 0.75                      | 15.08                  |
| 209.75             | 0.77                      | 16.64                  |
| 250.25             | 0.84                      | 20.06                  |
| 300.00             | 1.09                      | 26.64                  |