

High Power

Termination 50Ω, N-Male

TERM-25W-183N+

Typical Performance Data

FREQUENCY (MHz)	RETURN LOSS (dB)
10	56.31
20	55.19
30	53.82
40	52.52
50	50.94
60	50.32
70	49.49
80	48.79
90	48.24
100	47.67
200	44.32
300	41.81
400	39.85
500	38.24
600	36.90
700	35.74
800	34.75
900	33.92
1000	33.26
1500	32.36
2000	35.72
2500	56.78
3000	33.86
3500	27.88
4000	25.15
4500	24.18
5000	24.74
5500	26.99
6000	30.78
6500	34.02
7000	34.24
7500	32.08
8000	29.47
8500	27.67
9000	26.32
9500	26.13
10000	29.15
10500	39.34
11000	31.33
11500	29.12
12000	35.56
12500	28.71
13000	22.74
13500	21.61
14000	23.45
14500	26.87
15000	30.22
15500	35.81
16000	35.89
16500	31.65
17000	32.63
17500	28.05
18000	22.15