

Ultra Flexible Test Cable, SMA-Male/SMA-Male ULC-1.5FT-SMSM+

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
0.01	0.02	44.80	45.53
0.05	0.06	35.44	35.28
0.1	0.08	33.56	33.59
0.5	0.19	33.80	33.44
1.0	0.27	29.54	29.82
1.5	0.33	29.89	30.00
2.0	0.38	34.49	33.91
2.5	0.43	56.30	39.87
3.0	0.48	33.94	33.89
3.5	0.52	27.36	27.50
4.0	0.56	26.52	26.50
4.5	0.60	26.52	26.35
5.0	0.63	27.88	27.81
5.5	0.66	31.54	32.06
6.0	0.69	32.57	34.74
6.5	0.72	32.76	34.87
7.0	0.75	31.75	33.47
7.5	0.78	36.28	39.69
8.0	0.81	38.58	41.32
8.5	0.84	44.26	43.83
9.0	0.87	31.63	31.96
9.5	0.90	25.72	26.09
10.0	0.93	24.05	24.40
10.5	0.96	24.07	24.23
11.0	0.98	26.73	26.82
11.5	1.00	33.87	37.65
12.0	1.03	28.59	29.79
12.5	1.07	22.77	23.16
13.0	1.09	21.39	21.42
13.5	1.10	23.74	23.52
14.0	1.11	28.22	28.25
14.5	1.14	39.16	33.54
15.0	1.17	31.85	28.92
15.5	1.20	26.52	24.65
16.0	1.22	26.51	24.37
16.5	1.23	30.24	26.62
17.0	1.25	37.28	31.60
17.5	1.29	32.78	32.90
18.0	1.32	28.63	29.34

