

Adapter, Coaxial to Waveguide WR28-KFR+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	VSWR (:1)
26500	0.19	1.23
26750	0.18	1.19
27000	0.17	1.14
27250	0.16	1.12
27500	0.16	1.09
27750	0.16	1.06
28000	0.15	1.03
28250	0.15	1.04
28500	0.14	1.06
28750	0.14	1.08
29000	0.13	1.11
29250	0.14	1.12
29500	0.15	1.14
29750	0.17	1.15
30000	0.21	1.16
30250	0.25	1.17
30500	0.29	1.17
30750	0.31	1.17
31000	0.30	1.18
31250	0.27	1.18
31500	0.23	1.19
31750	0.19	1.20
32000	0.15	1.20
32250	0.12	1.20
32500	0.11	1.20
32750	0.11	1.21
33000	0.12	1.21
33250	0.13	1.22
33500	0.15	1.22
33750	0.15	1.23
34000	0.16	1.24
34250	0.17	1.24
34500	0.18	1.25
34750	0.19	1.25
35000	0.21	1.25
35250	0.23	1.25
35500	0.24	1.25
35750	0.25	1.25
36000	0.25	1.25
36250	0.24	1.24
36500	0.22	1.23
36750	0.21	1.22
37000	0.20	1.21
37250	0.18	1.20
37500	0.16	1.19
37750	0.15	1.18
38000	0.13	1.15
38250	0.12	1.14
38500	0.11	1.13
38750	0.10	1.12
39000	0.10	1.13
39250	0.09	1.14
39500	0.09	1.16
39750	0.09	1.21
40000	0.10	1.24