

Typical Performance Data

FREQUENCY (MHz)	ATTENUATION (dB)	VSWR (:1)
10	30.01	1.27
50	29.97	1.27
100	29.99	1.26
200	30.00	1.26
300	30.01	1.26
400	30.00	1.25
500	30.01	1.25
1000	30.01	1.24
1500	30.00	1.22
2000	29.98	1.20
2500	29.95	1.17
3000	29.94	1.14
3500	29.92	1.12
4000	29.93	1.09
4500	29.94	1.08
5000	29.98	1.09
5500	30.00	1.12
6000	30.04	1.16
6500	30.07	1.19
7000	30.13	1.20
7500	30.17	1.20
8000	30.21	1.18
8500	30.24	1.15
9000	30.28	1.13
9500	30.31	1.12
10000	30.35	1.12
10500	30.35	1.14
11000	30.39	1.15
11500	30.44	1.17
12000	30.47	1.18
12500	30.51	1.18
13000	30.55	1.18
13500	30.58	1.17
14000	30.64	1.18
14500	30.67	1.20
15000	30.71	1.23
15500	30.77	1.25
16000	30.81	1.25
16500	30.84	1.25
17000	30.85	1.22
17500	30.85	1.19
18000	30.89	1.17