

Typical Performance Data

FREQ.	INSERTION LOSS	VSWR	
		RF	RF + DC
(MHz)	(dB)	(:1)	(:1)
10	0.1	1.33	1.33
20	0.1	1.14	1.14
30	0.1	1.08	1.08
40	0.1	1.04	1.04
50	0.1	1.02	1.02
60	0.1	1.01	1.01
70	0.1	1.03	1.02
80	0.1	1.04	1.04
90	0.1	1.06	1.06
100	0.2	1.08	1.08
120	0.2	1.09	1.09
150	0.2	1.12	1.12
200	0.2	1.23	1.23
250	0.4	1.45	1.44
300	1.5	2.18	2.17
350	9.7	5.57	5.57
400	1.1	2.00	2.01
450	0.4	1.44	1.45
500	0.4	1.25	1.25
550	0.7	1.32	1.33
600	0.3	1.23	1.24
650	0.2	1.16	1.17
700	0.2	1.12	1.13
750	0.1	1.09	1.10
800	0.2	1.07	1.07
850	0.2	1.04	1.05
900	0.2	1.03	1.05
950	0.2	1.04	1.05
1000	0.2	1.02	1.04
1050	0.2	1.01	1.02
1100	0.2	1.01	1.02
1150	0.1	1.01	1.02
1200	0.1	1.02	1.04
1250	0.2	1.05	1.04
1300	0.2	1.05	1.04
1350	0.2	1.05	1.05
1400	0.2	1.06	1.06
1450	0.2	1.07	1.07
1500	0.2	1.08	1.08
1550	0.2	1.08	1.09
1600	0.2	1.09	1.10
1650	0.2	1.10	1.11
1700	0.2	1.10	1.11
1750	0.2	1.11	1.12
1800	0.2	1.12	1.13
1850	0.2	1.12	1.14
1900	0.2	1.13	1.14
1950	0.2	1.14	1.15
2000	0.3	1.14	1.16
2030	0.3	1.15	1.16
2050	0.3	1.15	1.17
2080	0.3	1.16	1.17
2100	0.3	1.16	1.18
2150	0.3	1.17	1.19