

Typical Performance Data

FREQ	INSERTION LOSS	VSWR	
		RF	RF & DC
(MHz)	(dB)	(:1)	
10.0	0.12	1.26	1.26
50.0	0.03	1.04	1.04
100.0	0.03	1.01	1.01
150.0	0.04	1.01	1.01
200.0	0.06	1.03	1.02
300.0	0.14	1.02	1.02
400.0	0.10	1.04	1.04
500.0	0.10	1.06	1.06
600.0	0.10	1.08	1.07
700.0	0.10	1.08	1.09
800.0	0.12	1.09	1.11
900.0	0.16	1.11	1.12
1000.0	0.20	1.13	1.14
1100.0	0.23	1.16	1.14
1200.0	0.26	1.18	1.15
1300.0	0.26	1.19	1.16
1400.0	0.24	1.20	1.17
1500.0	0.23	1.20	1.18
1600.0	0.20	1.18	1.19
1650.0	0.19	1.17	1.19
1700.0	0.16	1.16	1.20
1750.0	0.15	1.16	1.20
1800.0	0.17	1.16	1.21
1850.0	0.14	1.17	1.20
1900.0	0.15	1.17	1.21
1950.0	0.15	1.17	1.20
2000.0	0.12	1.19	1.21
2050.0	0.12	1.19	1.19
2100.0	0.12	1.21	1.20
2150.0	0.10	1.21	1.19
2200.0	0.09	1.23	1.20
2250.0	0.13	1.22	1.18
2300.0	0.12	1.22	1.19
2350.0	0.17	1.20	1.17
2400.0	0.22	1.20	1.17
2450.0	0.25	1.17	1.16
2500.0	0.28	1.17	1.17
2550.0	0.37	1.15	1.16
2600.0	0.30	1.15	1.17
2650.0	0.43	1.12	1.15
2700.0	0.37	1.12	1.16
2750.0	0.38	1.11	1.15
2800.0	0.37	1.11	1.16
2850.0	0.36	1.11	1.14
2900.0	0.34	1.12	1.15
2950.0	0.33	1.13	1.14
3000.0	0.34	1.14	1.15