

*Typical Performance Data*

FREQ	INSERTION LOSS	VSWR	
		RF	RF & DC
(MHz)	(dB)	(:1)	
1.0	0.47	1.16	1.06
2.0	0.37	1.10	1.07
3.0	0.35	1.09	1.08
4.0	0.34	1.08	1.07
5.0	0.34	1.08	1.07
6.0	0.33	1.08	1.08
7.0	0.33	1.08	1.08
8.0	0.33	1.08	1.08
9.0	0.33	1.08	1.08
10.0	0.33	1.08	1.08
20.0	0.36	1.08	1.08
30.0	0.40	1.09	1.09
40.0	0.44	1.10	1.10
50.0	0.48	1.11	1.11
60.0	0.49	1.11	1.11
70.0	0.49	1.11	1.11
80.0	0.49	1.11	1.11
90.0	0.48	1.10	1.10
100.0	0.46	1.10	1.10
200.0	0.41	1.08	1.08
300.0	0.40	1.07	1.08
400.0	0.39	1.08	1.08
500.0	0.41	1.09	1.09
600.0	0.41	1.09	1.11
700.0	0.43	1.11	1.12
800.0	0.42	1.11	1.14
900.0	0.44	1.13	1.16
1000.0	0.46	1.14	1.17
1100.0	0.48	1.15	1.18
1200.0	0.49	1.15	1.17
1300.0	0.44	1.15	1.17
1400.0	0.42	1.15	1.19
1500.0	0.42	1.15	1.20
1600.0	0.44	1.16	1.21
1700.0	0.45	1.15	1.21
1800.0	0.46	1.15	1.21
1900.0	0.47	1.14	1.21
2000.0	0.48	1.13	1.20
2100.0	0.49	1.12	1.19
2200.0	0.49	1.10	1.17
2300.0	0.49	1.09	1.14
2400.0	0.50	1.08	1.12
2500.0	0.53	1.08	1.10
2600.0	0.55	1.08	1.08
2700.0	0.58	1.09	1.07
2800.0	0.60	1.10	1.05
2900.0	0.60	1.12	1.04
3000.0	0.59	1.13	1.03