

Typical Performance Data

FREQ. (MHz)	PIN (dBm)	INSERTION LOSS with Current (RF port to RF&DC port) (dB)		ISOLATION (RF port to DC port) (RF&DC port to DC port) (dB)	VSWR (:1)
		0A	4A		
300.0	-8.74	0.53	0.59	17.67	1.14
450.0	-8.90	0.54	0.55	19.46	1.12
600.0	-8.81	0.44	0.39	20.53	1.11
700.0	-8.72	0.41	0.35	21.08	1.09
800.0	-8.86	0.60	0.76	21.50	1.09
1000.0	-8.89	0.53	0.49	22.45	1.10
1100.0	-8.97	0.59	0.54	22.94	1.06
1400.0	-9.15	0.46	0.41	24.22	1.08
1500.0	-9.14	0.45	0.40	24.73	1.09
1800.0	-8.85	0.49	0.44	25.97	1.10
1900.0	-8.90	0.50	0.45	26.45	1.10
2100.0	-9.02	0.52	0.47	27.30	1.09
2200.0	-9.11	0.50	0.44	27.68	1.10
2400.0	-9.19	0.52	0.44	27.99	1.09
2500.0	-9.20	0.50	0.45	28.42	1.09
2600.0	-9.27	0.52	0.47	28.46	1.08
2800.0	-9.40	0.56	0.55	28.20	1.06
3000.0	-9.48	0.63	0.63	27.73	1.04
3200.0	-9.50	0.72	0.67	27.24	1.04
3500.0	-9.58	0.82	0.77	26.95	1.12