



GF981
GF995

Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K
GF981	.150 (3.81)	.150 (3.81)	.032 (0.81)	.008 (0.20)	.036 (0.91)	.018 (0.46)	.062 (1.57)	.028 (0.71)	.022 (0.56)	.017 (0.43)
GF995			.065 MAX (1.65)							

CASE #	L	M	N	P	Q	R	S	T	WT. GRAM
GF981	.014 (0.36)	.036 (0.91)	.018 (0.46)	.062 (1.57)	.028 (0.71)	.037 (0.94)	.017 (0.43)	.014 (0.36)	.05
GF995									.06

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3Pl. $\pm .005$

Notes:

1. Open style, Ceramic Base.
2. Termination finish: Palladium Silver.

Mini-Circuits[®]

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified