


Outline Dimensions



* OVERALL CONNECTOR OR CABLE & BOOT DIM
[CONNECTOR SHAPE MAY VARY]

GM1530 SERIES
E-Z LOCK SMA MALE (CONN-1)
N MALE (CONN-2)

CASE STYLE #	A		B	C	D	E	T		WEIGHT GRAMS
	FEET	METERS					INCHES	MM	
GM1530-1.5	1.50	.46	.43 (10.92)	- -	.85 (21.59)	.787 (19.99)	+ .50/-0	+12.7/-0	61
GM1530-1.64	1.64	.50					+ .50/-0	+12.7/-0	63
GM1530-2	2.00	.61					+ .50/-0	+12.7/-0	68
GM1530-3	3.00	.91					+ .72/-0	+18.3/-0	82
GM1530-3.28	3.28	1.00					+ .79/-0	+20.0/-0	85
GM1530-4	4.00	1.22					+ .96/-0	+24.4/-0	95
GM1530-6	6.00	1.83					+1.44/-0	+36.6/-0	122
GM1530-6.56	6.56	2.00					+1.57/-0	+40.0/-0	130

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl. ± .03; 3Pl. ± .015

Note:

1. Flexible Coaxial Cable.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified