


### Outline Dimensions



KQ1506 SERIES  
SMA MALE (CONN-1)  
SMA MALE (CONN-2)

CASE STYLE #	A		B	C1	C2	D	E1	E2	F		T		WEIGHT GRAMS
	INCH	MM							141U-ASM+	141-ASM+	INCH	MM	
KQ1506-2	2.00	50.80									.05	1.27	6.89
KQ1506-3	3.00	76.20									.05	1.27	8.03
KQ1506-4	4.00	101.60									.05	1.27	9.17
KQ1506-5	5.00	127.00									.05	1.27	10.32
KQ1506-6	6.00	152.40									.05	1.27	11.46
KQ1506-7	7.00	177.80									.10	2.54	12.60
KQ1506-8	8.00	203.20									.10	2.54	13.74
KQ1506-9	9.00	228.60									.10	2.54	14.89
KQ1506-10	10.00	254.00									.10	2.54	16.03
KQ1506-11	11.00	279.40									.10	2.54	17.17
KQ1506-12	12.00	304.80	.36	.315	.250	.36	.315	.250	.141 $\nabla$ .003	.163 $\nabla$ .004	.10	2.54	18.32
KQ1506-13	13.00	330.20	(9.14)	(8.00)	(6.35)	(9.14)	(8.00)	(6.35)	(3.58 $\nabla$ 0.07)	(4.14 $\nabla$ 0.10)	.15	3.81	19.46
KQ1506-14	14.00	355.60									.15	3.81	20.60
KQ1506-15	15.00	381.00									.15	3.81	21.75
KQ1506-16	16.00	406.40									.15	3.81	22.89
KQ1506-17	17.00	431.80									.15	3.81	24.03
KQ1506-18	18.00	457.20									.15	3.81	25.17
KQ1506-19	19.00	482.60									.15	3.81	26.32
KQ1506-19.7	19.69	500.00									.15	3.81	27.12
KQ1506-20	20.00	508.00									.15	3.81	27.45
KQ1506-22	22.00	558.80									.15	3.81	29.75
KQ1506-24	24.00	609.60									.15	3.81	32.03

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl.  $\pm$  .03; 3Pl.  $\pm$  .015

**Note:**

1. 141 Hand-Flex™ Coaxial Cable.
2. "A" Represents Length of Cable.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

# Case Style

# KQ

## KQ1506

### Outline Dimensions

KQ1506 SERIES  
SMA MALE (CONN-1)  
SMA MALE (CONN-2)

CASE STYLE #	A		B	C1	C2	D	E1	E2	F		T		WEIGHT GRAMS							
	INCH	MM							141U-ASM+	141-ASM+	INCH	MM								
KQ1506-26	26.00	660.40	.36 (9.14)	.315 (8.00)	.250 (6.35)	.36 (9.14)	.315 (8.00)	.250 (6.35)	.141 $\forall$ .003 (3.58 $\forall$ 0.07)	.163 $\forall$ .004 (4.14 $\forall$ 0.10)	.20	5.08	34.32							
KQ1506-30	30.00	762.00									.20	5.08	38.89							
KQ1506-32	32.00	812.80									.20	5.08	41.18							
KQ1506-36	36.00	914.40									.30	7.62	45.75							
KQ1506-39.4	39.37	1000.00									.30	7.62	49.63							
KQ1506-40	40.00	1016.00									.30	7.62	50.32							
KQ1506-48	48.00	1219.20									.40	10.16	61.75							
KQ1506-50	50.0	1270.00									.40	10.16	72.15							
KQ1506-59.1	59.06	1500.00									.40	10.16	73.18							
KQ1506-60	60.00	1524.00									.40	10.16	73.18							
KQ1506-72	72.00	1828.80									.40	10.16	86.90							
KQ1506-78.7	78.74	2000.00									.40	10.16	94.55							

Unless otherwise specified dimensions are in inches (mm).  
Tolerances: 2Pl.  $\pm$  .03; 3Pl.  $\pm$  .015