


### Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	M
KR1508	.670 (17.02)	1.505 (38.23)	.285 (7.24)	.236 (5.99)	.280 (7.11)	.079 (2.01)	.108 (2.74)	.138 (3.51)	.710 (18.03)	1.545 (39.24)	.100 (2.54)	.300 (7.62)

CASE#	N	P	Q	R	S	T	U	V	W	WT, GRAMS
KR1508	.394 (10.01)	.158 (4.01)	.222 (5.64)	.187 (4.75)	.080 (2.03)	1.245 (31.62)	0.410 (10.41)	0.192 (4.88)	.238 (6.05)	9.8

Dimensions are in inches (mm). Tolerances: 2Pl.  $\pm .03$ ; 3Pl.  $\pm .015$

1. Case material: Nickel-Silver alloy.
2. Base: Printed wiring laminate.
3. Termination finish:  
For RoHS Case Styles: 2-5  $\mu$  inch (.05-.13 microns) Gold over 120-240  $\mu$  inch (3.05-6.10 microns) Nickel plate.  
All models, (+) suffix.