



Case Style

LV

Outline Dimensions


LV1753



INSTRUCTION FOR MOUNTING BRACKETS:
 TOOL REQUIRED: PHILLIPS HEAD SCREW DRIVER
 STEP 1: REMOVE RUBBER FEET FROM THE BOTTOM OF THE UNIT.
 DO NOT DISCARD THE FASTENERS.
 STEP 2: MOUNT THE BRACKETS WITH THE FASTENERS REMOVED IN STEP 1, USING THE COUNTER BORE HOLES IN THE BRACKET.

FRONT VIEW

BACK VIEW



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	P	WT. GRAMS
LV1753	11.00 (279.4)	8.50 (215.9)	2.15 (54.6)	.28 (7.1)	.60 (15.2)	0.75 (19.05)	8.37 (212.6)	1.50 (38.1)	.18 (4.6)	7.870 (199.9)	.158 (4.0)	.25 (6.35)	0.850 (21.6)	0.40 (10.2)	2500

Dimensions are in inches (mm). Tolerances: 2PL. +/- .03; 3PL. +/- .015

Notes:

1. Case material: Aluminum.



INTERNET <http://www.minicircuits.com>
 P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
 Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
 Mini-Circuits ISO 9001 & ISO 14001 Certified